## Code: HDMI+USB-EX-60 EXTENDER HDMI+USB-EX-60 Net: 87.01 EUR Gross: 87.01 EUR

Device allows to send High Definition signal to the TV-Set receiver equipped with HDMI connector via UTP Cat. 5e, 6 cable. Extender also allows to extend an USB 2.0 port, eg. in order to control the recorder using the mouse. To TV set you need connect only one UTP cable, what makes installation easy and improve aesthetic quality of installation.

The HDMI+USB-EX-60 is a more recent device compared to HDMI+USB-EX-100 model. Despite the smaller range, the use of a higher sampling frequency definitely improved the image quality and the comfort of the mouse operations.



### SPECIFICATION

Supported HDMI resolutions:	480p, 576p, 720p, 1080p
Maximal transmission range:	• 60 m UTP cat. 6 • 50 m UTP cat. 5, 5e
Main features:	<ul> <li>Extender also allows to extend an USB 2.0 port, eg. in order to control the recorder using the mouse</li> <li>Audio transmission via network</li> </ul>
Main features:	<ul> <li>Very good image quality with no visible distortions caused by compression</li> <li>No delays in video transmission</li> <li>No delays in mouse control operations</li> <li>Possibility to power only the transmitter (in the set there is one power adapter)</li> <li>Transition of the HDMI signal in the transmitter</li> </ul>
Power supply:	<ul> <li>Transmitter 5 V DC / 2 A (power adapter included)</li> <li>Receiver 5 V / 2 A (optional)</li> </ul>
Operation temp:	0 °C 60 °C
Permissible relative humidity:	0 % 90 % (non-condensing)
Weight:	0.13 kg
Dimensions:	93.5 x 80 x 18 mm - Transmitter or receiver dimensions
Guarantee:	2 years

#### PRESENTATION

Transmitter and receiver connectors:






Top view:



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60



Connection schematic diagram:



#### **OUR OPINIONS**

# Ð

- $\circ$  The HDMI+USB-EX-60 is a more recent device compared to HDMI+USB-EX-100 model. Despite the smaller range, the use of a higher sampling frequency definitely improved the image quality and the comfort of the mouse operations.
- $\circ\;$  Very good image quality with no visible distortions caused by compression.
- $\circ~$  No delays in signal transmission.

#### PACKAGE

Dimensions (L x W x H): 0x0x0 mm Gross Weight: 0 kg



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60