

Warning!

Please read the user manual included in this work as it contains important information related with safety of installation and use of the device.

Only persons who read the user manual may use the device.

The user manual must be kept because it may be required in the future. The device is to be used exclusively for purposes specified in this user manual.

The device must be unpacked prior to starting-up. After removing the packaging make sure the device is in working order. If the product has defects, it should not be used until it is repaired.

The product is intended for use at home and commercial use and may not be used for other than intended use.

The manufacturer is not liable for damages resulting from not adhering to the rules contained in the user manual, therefore, we recommend to follow the aforementioned safety rules for operation and maintenance of the device. In this way you will ensure yourself safety and avoid causing damage to the device.

The manufacturer and the supplier are not liable for losses or damages arising out of the product, including financial or intangible losses, loss of profits, income, data, pleasure from use of the product or other products related with it - indirect, incidental or consequential loss or damage. The above provisions apply whether the loss or damage concerns:

1. Deterioration of quality or the lack of operation of the products or products related with it due to damage as well as the lack of access to the product when it is undergoing repair, which results in stoppage the loss of user's time or a break in business activity; 2. Improper results of operation of the product or products related with it;

3. It applies to losses and damages according to any legal category, including negligence and other losses, termination of a contract, expressed or implied guarantee and strict liability (even if the manufacturer or the supplier was notified about the possibility of occurrence of such damages).

Safety measures:

Particular attention at designing was directed to quality standards of the device where ensuring safety of operation is the most important factor.

The device must be secured against contact with caustic, staining and viscous fluids.

The device was designed in such a way that it restarts operation when power supply is restored after a break.

Attention! We recommend using protections to further protect the device from possible overvoltages in installations. Surge protectors are effective protection against accidental pass to the device voltages higher than the rated. Damages caused by pass the voltages higher than specified in manual, are not under warranty.

Turn off the device before transporting it.

Prior to connecting the device to a power source check whether the supplied voltage is consistent with rated voltage specified in the user manual.

Proper product disposal:

A marking of a crossed out waste bin indicates that the product may not be disposed together with other household waste in the entire EU. To avoid possible damage to the natural environment of health due to uncontrolled waste disposal, therefore, it should be handed over for recycling, propagating in this way sustainable use of natural resources.

To return a worn-out product, use a collection and disposal system of this type of equipment or contact a seller from whom it was purchased. He will then be recycled in an environmentally-friendly way.





cameras.

image at night mode.

IP camera with efficient H.264 image compression algorithm for clear and smooth video streaming at maximal resolution of 3 MPx. Very easy operation by Internet Explorer browser allows the users to convenient and remote support, and also remote management of the camera. Included camera software enables management and integrated monitoring of many network

 $\ensuremath{\text{ICR}}$ - The movable IR filter allows to perfect colors reproduction in daylight and wide gray-scale with high sharpness of the

User Manual Code: DH-IPC-HFW1320SP IP CAMERA **DH-IPC-HFW1320SP** -0360B 3.0 Mpx 3.6 mm DAHUA

Standard: TCP/IP 1/3 " Progressive Scan CMOS Sensor: Matrix size: 3.0 Mpx Scanning system: Progressive 2304 x 1296 - 3 Mpx 1920 x 1080 - 1080p Resolution: 1280 x 1024 - 1.4 Mpx 1280 x 960 - 1.3 Mpx 1280 x 720 - 720p Lens: 3.6 mm 81 ° (manufacturer data)
76 ° (our tests result) View angle: Range of IR illumination: 30 m S/N ratio: > 50 dB RS-485 interface: _ Memory card slot: _ H.264 / MJPEG Image compression method: Alarm inputs / outputs: _ Audio: Bitrate: 4 ... 8192 kbps - H.264 Main stream frame rate: 20 fps @ 2048x1536



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60

DH-IPC-HFW1320SP



User Manual Code: DH-IPC-HFW1320SP IP CAMERA DH-IPC-HFW1320SP -0360B 3.0 Mpx 3.6 mm DAHUA

Network interface:	10/100 Base-T (RJ-45)
Network protocols:	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP, ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour
WEB Server:	Built-in
Max. number of on-line users:	20
ONVIF:	2.4
Main features:	 3D-DNR - Digital Noise Reduction D-WDR - Wide Dynamic Range BLC/HLC - Back Light / High Light Compensation Possibility to change the resolution, quality and bit rate Configurable Privacy Zones Mirror - Mirror image
Color:	White
Power supply:	• PoE (802.3af) • 12 V DC / 400 mA
Mobile phones support:	 Port no.: 37777 or access by a cloud (P2P) Android: Free application <u>DMSS</u> iOS (iPhone): Free application <u>DMSS</u> There are also paid versions of mobile applications: gDMSS Plus, iDMSS Plus, wDMSS plus
Housing:	Compact - Metal
Operation temp:	-30 °C 60 °C
"Index of Protection":	IP67
Weight:	0.38 kg
Dimensions:	Ø 70 x 165 mm
Supported languages:	English, Polish
Manufacturer / Brand:	DAHUA
Guarantee:	3 years



DH-IPC-HFW1320SP





Side view:



Camera mounting side view:









Example captures of device interface:



DH-IPC-HFW1320SP







PACKAGE

Dimensions (L x W x H): 0x0x0 mm Gross Weight: 0 kg



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60