

## Warning!

Please read the user manual included in this work as it contains important information related with safety of installation and use of the device.

Only persons who read the user manual may use the device.

The user manual must be kept because it may be required in the future. The device is to be used exclusively for purposes specified in this user manual.

The device must be unpacked prior to starting-up. After removing the packaging make sure the device is in working order. If the product has defects, it should not be used until it is repaired.

The product is intended for use at home and commercial use and may not be used for other than intended use.

The manufacturer is not liable for damages resulting from not adhering to the rules contained in the user manual, therefore, we recommend to follow the aforementioned safety rules for operation and maintenance of the device. In this way you will ensure yourself safety and avoid causing damage to the device.

The manufacturer and the supplier are not liable for losses or damages arising out of the product, including financial or intangible losses, loss of profits, income, data, pleasure from use of the product or other products related with it - indirect, incidental or consequential loss or damage. The above provisions apply whether the loss or damage concerns:

1. Deterioration of quality or the lack of operation of the products or products related with it due to damage as well as the lack of access to the product when it is undergoing repair, which results in stoppage the loss of user's time or a break in business activity; 2. Improper results of operation of the product or products related with it;

3. It applies to losses and damages according to any legal category, including negligence and other losses, termination of a contract, expressed or implied guarantee and strict liability (even if the manufacturer or the supplier was notified about the possibility of occurrence of such damages).

## Safety measures:

Particular attention at designing was directed to quality standards of the device where ensuring safety of operation is the most important factor.

The device must be secured against contact with caustic, staining and viscous fluids.

The device was designed in such a way that it restarts operation when power supply is restored after a break. Turn off the device before transporting it.

Prior to connecting the device to a power source check whether the supplied voltage is consistent with rated voltage specified in the user manual.

Attention! We recommend using protections to further protect the device from possible overvoltages in installations. Surge protectors are effective protection against accidental pass to the device voltages higher than the rated. Damages caused by pass the voltages higher than specified in manual, are not under warranty.

## Proper product disposal:

A marking of a crossed out waste bin indicates that the product may not be disposed together with other household waste in the entire EU. To avoid possible damage to the natural environment of health due to uncontrolled waste disposal, therefore, it should be handed over for recycling, propagating in this way sustainable use of natural resources.

To return a worn-out product, use a collection and disposal system of this type of equipment or contact a seller from whom it was purchased. He will then be recycled in an environmentally-friendly way.

It is forbidden to use the device in case its power cord or plug is damaged, the device works incorrectly, was damaged or dropped. A damaged power cord or plug must be replaced with new ones by the manufacturer, personnel of service centre or a person with relevant qualifications in order to avoid the risk of electric shock. We do not recommend repairing the device on one's own for safety reasons.

The device is not intended for operation by persons (including children) with limited physical, sensory or mental capabilities as well as persons inexperienced in operation or not competent to operate of such device, unless the operation is supervised by a person responsible for their safety or in line with instructions for use provided by such person.

It is forbidden to touch the plug with wet hands! Pull the plug, never the cable, to pull out the plug from a socket.

The device is to be used exclusively according to its use described in this manual. Use of accessories not recommended by the manufacturer of the device may cause fire, electric shock or injuries.

Marking of a lightning inside a equilateral triangle signifies presence of dangerous voltage, contained under the cover of the device. It may be dangerous for user's life and health.







Standard:	TCP/IP	
Supported resolutions:	32 @ 4000 x 3000 px, 32 @ 3840 x 2160 px, 32 @ 3072 x 2048 px, 32 @ 2592 x 1944 px, 32 @ 2560 x 1944 px, 32 @ 2560 x 1440 px, 32 @ 2048 x 1536 px, 32 @ 1920 x 1536 px, 32 @ 1920 x 1080 px, 32 @ 1280 x 720 px, 32 @ 704 x 576 px	
Video outputs:	1 pcs HDMI 1 pcs VGA There is a possibility to configure a SPOT function on one of the output	
Audio support:	<ul><li>32 Channels - Audio from cameras</li><li>Bi-directional audio streaming support</li></ul>	
Audio inputs:	1 pcs CINCH	
Audio outputs:	1 pcs CINCH	
Image compression method:	H.265 / H.264 / H.264+ / MPEG-4	
Maximal total frame rate:	800 fps @ 4000 x 3000 px, 800 fps @ 3840 x 2160 px, 800 fps @ 3072 x 2048 px, 800 fps @ 2592 x 1944 px, 800 fps @ 2560 x 1944 px, 800 fps @ 2560 x 1440 px, 800 fps @ 2048 x 1536 px, 800 fps @ 1920 x 1536 px, 800 fps @ 1920 x 1080 px, 800 fps @ 1280 x 720 px, 800 fps @ 704 x 576 px	
Supported hard drives:	2 x 10 TB SATA III	
Recording modes:	Manual, Sensor, Motion detection, Schedule	
Network protocols:	TCP/IP, PPPoE, DHCP, Hik Cloud P2P, DNS, DDNS, NTP, SADP, NFS, iSCSI, UPnP, HTTPS, ONVIF	
External storage devices backup:	Backup to USB drive (pendrive, external drive)	





## User Manual Code: DS-7632NI-I2 NVR **DS-7632NI-I2** 32 CHANNELS Hikvision

Searching and playback the records:	Records searching: by time and events type. Records playback: forward, backward, fast, slow Advanced searching (to the one second accuracy) All channels synchronous playback, Smart Search function Records playback from max. 16 channels in the same time @ 1080p or max. 4 @ 4K	
Bitrate:	max. 256 Mbps	
Network functions:	<ul> <li>Live image view, Playback the records, Backup the records</li> <li>max. 128 on-line users - iVMS-4200 application</li> <li>ANR - Automatic Network Replenishment allows to save image to the card when the network connection with DVR is break (network failure) and next synchronize its</li> </ul>	
ONVIF:	✓	
Mobile phones support:	Port no.: 8000 or access by a cloud (P2P) Android: Free application <u>iVMS-4500</u> or <u>Hik-Connect</u> iOS (iPhone): Free application <u>iVMS-4500</u> or <u>Hik-Connect</u>	
Default IP address:	192.168.1.64	
Default admin user / password:	admin / -	
Web browser access ports:	80, 8000	
PC client access ports:	8000	
Mobile client access ports:	8000	
RTSP URL:	<ul> <li>rtsp://user:password@192.168.1.64:554/Streaming/Channels/channel_no01/ - Main stream</li> <li>rtsp://user:password@192.168.1.64:554/Streaming/Channels/channel_no02/ - Sub stream</li> </ul>	
Alarm inputs / outputs:	4 / 1	
PTZ control:	~	
Motion Detection:	22 x 18 motion zones	
Intelligent Image Analysis:	×	
Mouse support:	×	
IR remote controller in the set:	-	
Power supply:	12 V DC / 3.33 A (power adapter included)	
Weight:	1.80 kg	
Dimensions:	380 x 325 x 52 mm	
Supported languages:	English, Bulgarian, Croatian, Czech, Danish, Estonian, French, Greek, Spanish, Dutch, Lithuanian, Latvian, German, Norwegian, Polish, Portuguese, Russian, Romanian, Serbian, Slovak, Slovenian, Swedish, Turkish, Hungarian, Italian	
Country of origin:	China	
Manufacturer / Brand:	Hikvision	
SAP Code:	303602918	
Guarantee:	3 years	

Front panel:







Rear panel:



See how to mount a hard disk drive and configure the recorder:

In the kit:



PACKAGE

Dimensions (L x W x H): 0x0x0 mm	Gross Weight: 0 kg
----------------------------------	--------------------



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60

2024-04-19

DS-7632NI-I2