

Warning!

Please read the user manual included in this work as it contains important information related with safety of installation and use of the device.

Only persons who read the user manual may use the device.

The user manual must be kept because it may be required in the future. The device is to be used exclusively for purposes specified in this user manual.

The device must be unpacked prior to starting-up. After removing the packaging make sure the device is in working order. If the product has defects, it should not be used until it is repaired.

The product is intended for use at home and commercial use and may not be used for other than intended use.

The manufacturer is not liable for damages resulting from not adhering to the rules contained in the user manual, therefore, we recommend to follow the aforementioned safety rules for operation and maintenance of the device. In this way you will ensure yourself safety and avoid causing damage to the device.

The manufacturer and the supplier are not liable for losses or damages arising out of the product, including financial or intangible losses, loss of profits, income, data, pleasure from use of the product or other products related with it - indirect, incidental or consequential loss or damage. The above provisions apply whether the loss or damage concerns:

1. Deterioration of quality or the lack of operation of the products or products related with it due to damage as well as the lack of access to the product when it is undergoing repair, which results in stoppage the loss of user's time or a break in business activity; 2. Improper results of operation of the product or products related with it;

3. It applies to losses and damages according to any legal category, including negligence and other losses, termination of a contract, expressed or implied guarantee and strict liability (even if the manufacturer or the supplier was notified about the possibility of occurrence of such damages).

Safety measures:

Particular attention at designing was directed to quality standards of the device where ensuring safety of operation is the most important factor.

The device must be secured against contact with caustic, staining and viscous fluids.

The device was designed in such a way that it restarts operation when power supply is restored after a break.

Attention! We recommend using protections to further protect the device from possible overvoltages in installations. Surge protectors are effective protection against accidental pass to the device voltages higher than the rated. Damages caused by pass the voltages higher than specified in manual, are not under warranty.

Turn off the device before transporting it.

Prior to connecting the device to a power source check whether the supplied voltage is consistent with rated voltage specified in the user manual.

Proper product disposal:

A marking of a crossed out waste bin indicates that the product may not be disposed together with other household waste in the entire EU. To avoid possible damage to the natural environment of health due to uncontrolled waste disposal, therefore, it should be handed over for recycling, propagating in this way sustainable use of natural resources.

To return a worn-out product, use a collection and disposal system of this type of equipment or contact a seller from whom it was purchased. He will then be recycled in an environmentally-friendly way.







The S-21 allows to measure the TV signals at DVB-S/S2/S2X installations. Readable menu will help the operation for any installer.

| Output and input: | 1 pcs F socket, 1 pcs micro USB, 1 pcs 2.1/5.5 mm socket | |
|-----------------------------------|--|--|
| Display: | 2.4 " TFT LCD | |
| Frequency range: | 950 MHz 2150 MHz - DVB-S / DVB-S2 / DVB-S2X | |
| Signal level: | -2565 dBm | |
| LNB power supply: | 13 / 18 V, 350 mA | |
| Switching between bandwidths: | 0 / 22 kHz | |
| DiSEqC: | DiSEqC 1.0, 1.1, 1.2, USALS systems support | |
| Antenna powering: | - | |
| Video signal test: | - | |
| Programming and firmware upgrade: | via micro USB port | |
| Battery power supply: | Li-Ion battery 7.4 V / 2500 mAh 12 V / 1 A (power adapter included) | |





| Main features: | Measurement of signal strength and quality Signal indicator : LED display / Beep signal Measurement of BER, PWR, SNR Spectrum measurement mode Support for a satellite dish motor Constellation diagram UNICABLE technology support Support loop search function (signal preview on 8 frequencies simultaneously) Signal lock audible notification Clear graphical interface OSD menu full in Polish Long standby time Low power consumption Compass Flashlight built-in Illuminated buttons Anti-shock silicone case |
|-----------------------|---|
| Weight: | 0.29 kg |
| Dimensions: | 166 x 94 x 41 mm |
| Supported languages: | Polish, English, French, Spanish, German, Portuguese, Russian, Italian |
| Manufacturer / Brand: | Spacetronik |
| Guarantee: | 2 years |

Front panel:



Side view:







Top view:



Rear view:








OSD menu:



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60

2024-04-27






| Signal Sci | N |
|---|-------------------------------------|
| SAT: TelStar.18 - Ku TP: 13 £ 138.0 000000 12721 V 43200 LNB: 11300 11300 11300 D1.0:4 MER: 0.0E+0 Metcoler | PWR dBuv 4.40 syn: dB 0.00 |
| S: | 6% 0% |











| Sat Manage 🛛 🗰 | | |
|----------------|---------------------|-----------|
| 901 | E 26.0 Badr | |
| 9412 | W 7.0 Nilesat 201 | |
| 997 | E 13.8 HotBird | |
| 894 | E 52.5 YAHSAT | |
| 005 | E S3.0 Express AM6 | |
| DDE | E 42.0 Turksat | |
| IF11 | Add [F2] Del [] TP | IOKI Edit |

| Sys | 1111 | | |
|-----------------|-----------------------------|--|--|
| OSD Language | English | | |
| Key Tone | OFF | | |
| Local Longitude | E 118.6 | | |
| Local Latitude | N 24.9 | | |
| PWR Unit | dBuV | | |
| BG Color | color 1 | | |
| Reset Factory | 0K. | | |

VF-8920E [B2022-07-07]

In the kit:



PACKAGE

Dimensions (L x W x H): 0x0x0 mm Gross Weight: 0 kg



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60